

## 0.1mg Analytical Balance NA



## Feature:

The visual appearance of the product is blent into the simple concept, stylish and generous. Specially makes the fine pouring cast- aluminium outer covering, soas to enhance the balance of the anti-static anti-jamming capability. The panel with five operational button, Sliding glass windscreen provide big space, insightful vision and operate easily. We use high precision magnet sensor to keep the weighing more fast and stable.

•Magnet sensor keep weighing stable and fast

•Full range tare, Counting, Units choose ...

•RS 232 Interface can connect the computer and printer.

## Specification:

NA1004	NA1104	NA1204	NA2004	NA2104	NA2204	NA2604
100g	110g	120g	200g	210g	220g	260g
1						
0.0001g (0.1mg)						
±0.0002g						
±0.0003g						
≤3s						
17.5℃~22.5℃						
Ф80mm						
340*215*350 (LxWxH) mm						
Power Line						
EXTERNAL						
6.5kg						
10.0kg						
470X320X490 (LxWxH) mm						
RS232						
				100g 110g 120g 200g 0.0 100g 110g 120g 200g 0.0 100g 120g 120g 120g 120g 120g 120g 120g	100g 110g 120g 200g 210g   I I 0.0001g (0.1m 0.0002g ±0.0002g   ±0.0003g ±0.0003g ≤3s ≤3s   I I IIII (0.1m) 10002g   ±0.0003g ≤3s 17.5°C ~22.5   Ø80mm 340*215*350 (LxW)   Power Line EXTERNAL   IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII	$\begin{array}{ c c c } \hline 100g & 110g & 120g & 200g & 210g & 220g \\ \hline \  & & & & & & \\ \hline \  & & \\ \hline \ \  & & \\ \hline \  & & \\ \hline \  & & \\ \hline \  & \  &$